



**GENLYTE**  
**SOLUTIONS**

a Signify business

# Warehouse Product Guide

2025




# Tackle your lighting project quickly

Tight project timelines can't hold you back; get quality lighting delivered within 5-10 shipping days. Our solutions can light the way for your next project with the Design Ready portfolio.

The selected QuickShip, high performance LED lamps and award-winning luminaires from Genlyte Solutions brands include Lightolier, Day-Brite, Chloride, and Stonco Keene offerings.

## Illuminate your space with ease

Genlyte Solutions provides the lighting solution for every project. Whether it's lighting and connecting your public spaces, giving your space an energy-saving upgrade, or working on a yet-to-be constructed project, we've got you covered. Our Design Ready portfolio makes it easy for you to find highly configurable lighting with modern designs within your timeline and your budget.



# Design Build

Our stocking solutions are  
now ready to go with your  
stock and design ready needs



## Stock ready

Stock and Flow  
Ships in **2 days**



## Design ready


Design Build  
Ships in **5-10 days**



# Warehouse applications

## Around the clock lighting solutions

Lighting can account for a significant portion of a warehouse's energy bill, so it must be as efficient and cost-effective as possible when running 24/7. Longer-lasting and energy-efficient LED lighting can have an enormous impact on your bottom line, reducing operational costs through reduced downtime and lower energy consumption while providing a sense of security on the work floor.





# Day-Brite

# FBZ High Bay

Product highlight

## Best in class optics with less fixtures

FBZ's targeted optics solution puts the lighting where you need it all while offering you a leaner design resulting in fewer luminaires and less complexity.

## Better overall efficiency<sup>1</sup>

A 13% overall improved efficacy rating contributes to a better overall cost of ownership.



On average, a typical application with FBZ versus alternate products can use

**up to 38%<sup>2</sup>**  
fewer fixtures



1. Based on a typical warehouse aisle application (10' x 300' x 28') using closest competitor comparison luminaires. Actual savings may vary depending on application.

2. Compared to our previous generation luminaire.

Stock  
ready

2 day  
shipping

Design  
ready

5-10 day  
shipping

# Storage, Production & Manufacturing

## High Bay (rectangular) luminaires

Day-Brite



### FCY High Bay

- Convenient specification
- Multiple lumen options
- Standard 0-10V dimming
- Simple mounting methods
- Color selectable 4000K/5000K

Stock  
ready

Day-Brite



### FBZ High Bay

- Targeted optics solution
- Reduced total cost of ownership with lower capital investment and lower energy costs
- Advanced smart lighting capabilities with adaptive and future proof controls

Design  
ready

Day-Brite



### FHG High Bay

- 12,000-60,000 lumens for versatile applications
- Metal housing with excellent thermal management
- 0-10V dimming and sensor-compatible
- 100,000+ hour lifespan, surge protection, and UL listed

Design  
ready

## High Bay (round) luminaire

Day-Brite



### HCY High Bay

- Multiple lumen options
- Simple mounting methods
- Color selectable 4000K/5000K
- Field mount microwave sensor and programming remote
- Lumen selectable large size 28,000/33,000

Stock  
ready

## Recessed Troffer

Day-Brite



### Selectable Troffer (DSRT)

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock  
ready





## Industrial Linear

### Day-Brite



#### V3W Vaporlume

- Ideally suited for use in refrigerated cold storage, industrial, parking garage, and canopy applications
- Acceptable for outdoor as well as indoor installations
- NSF Certified option for Non-Food Zone/Splash Zone installations

Stock  
ready

Design  
ready

### Day-Brite



#### VTS Sealed Strip

- Acceptable for outdoor and indoor installations
- Can be surface mounted or suspended
- Selectable default setting is 4000K correlated CCT with max available power

Stock  
ready

## General Purpose Linear

### Day-Brite



#### FluxStream Strip

- 2', 3', 4' and 8' tandem lengths available to accommodate many field applications
- Frosted acrylic diffuser provides wide light distribution, superior glare control
- Diffuser and LED plate snap into place allowing tool-free access

Stock  
ready

Design  
ready

### Day-Brite



#### FluxSpace Strip

- 4 different styles in a 4" housing
- State of the art smart lighting capabilities with adaptive and future proof controls
- Endless possibilities for a host of applications

Design  
ready

Stock  
ready

2 day  
shipping

Design  
ready

5-10 day  
shipping

# Packing, Staging, Shipping & Docking

## High Bay (rectangular) luminaires

Day-Brite



### FCY High Bay

- Convenient specification
- Multiple lumen options
- Standard 0-10V dimming
- Simple mounting methods
- Lumen output selectable

Stock  
ready

Day-Brite



### FBZ High Bay

- Targeted optics solution
- Reduced total cost of ownership with lower capital investment and lower energy costs
- Advanced smart lighting capabilities with adaptive and future proof controls

Design  
ready

## High Bay (round) luminaire

Day-Brite



### HCY High Bay

- Multiple lumen options
- Simple mounting methods
- Color selectable 4000K/5000K
- Field mount microwave sensor and programming remote
- Lumen selectable large size 28,000/33,000

Stock  
ready

## Recessed Troffer

Day-Brite



### Selectable Troffer (DSRT)

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock  
ready





## Industrial Linear

### Day-Brite



### V3W Vaporlume

- Ideally suited for use in refrigerated cold storage, industrial, parking garage, and canopy applications
- Acceptable for outdoor as well as indoor installations
- NSF Certified option for Non-Food Zone/Splash Zone installations

Stock  
ready

Design  
ready

## General Purpose Linear

### Day-Brite



### FluxStream Strip

- 2', 3', 4' and 8' tandem lengths available to accommodate many field applications
- Frosted acrylic diffuser provides wide light distribution, superior glare control
- Diffuser and LED plate snap into place allowing tool-free access

Stock  
ready

Design  
ready

### Day-Brite



### FluxSpace Strip

- 4 different styles in a 4" housing
- State of the art smart lighting capabilities with adaptive and future proof controls
- Endless possibilities for a host of applications

Design  
ready

### Day-Brite



### SDS Selectable Strip

- Frosted glare-free lens
- Simple mounting method
- CCT & Lumen selectability
- Durable construction
- Ease of installation and maintenance
- Sensor Ready

Stock  
ready

Stock  
ready

2 day  
shipping

Design  
ready

5-10 day  
shipping

# General Illumination



## Recessed Troffers

Day-Brite



### FluxPanel Selectable

- Low glare
- Wireless control options available
- NSF rating is offered as standard for areas with high sanitization needs
- DLC listed

Stock  
ready

Design  
ready

Day-Brite



### FluxGrid Recessed

- High quality and performance for optimum energy savings
- Drivers and boards are easily accessible from below
- 3-1/8" deep low profile configuration
- Wireless control options available

Stock  
ready

Design  
ready

Day-Brite



### Selectable Troffer (DSRT)

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock  
ready

## Downlights

LIGHTOLIER



### ModuLyte

- 4", 6", and 8" round apertures
- Frame-optional architecture for new, remodel, and retrofit construction
- Lumen selectable (500-5000lm) and color selectable (2700K, 3000K, 3500K, 4000K, 5000K)

Stock  
ready

LIGHTOLIER



### LyteProfile

- The combined light engine and reflector allow tool-free installation
- Standard 120/277V frame simplifies planning and installation
- UniFrame infrastructure allows 50K+ product configurations

Stock  
ready

Design  
ready

LIGHTOLIER



### Commercial Retrofit

- 4 sizes to accommodate applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock  
ready



# Security & Outdoor

## Security Exit/ Emergency luminaires

CHLORIDE



### Value+

- Snap together design
- Nicad battery
- Smaller compact housing
- Operating temperature range: 10°C (50°F) to 40°C (104°F)

Stock  
ready

Design  
ready

## Outdoor Floodlighting

Stonco KEENE



### SlimFlood Selectable

- Can be mounted on the ground, wall, or pole
- Field selectable CCT of 3000K-5000K
- Field Adjustable Optics
- IP65 rated, 5-year limited warranty

Stock  
ready

## Outdoor Canopy

Stonco KEENE



### Garage & Canopy

- IP65 rated luminaire
- Die-cast round housing protect LEDs and driver
- DLC Premium
- 10kV surge protection
- 120-347V

Stock  
ready

## Outdoor Wall Pack

Stonco KEENE



### LytePro Wall

- Low-profile design
- Three sizes to accommodate multiple mounting heights
- Optical distributions offer full cutoff performance and excellent uniformity for precise wall and area illumination

Stock  
ready

Design  
ready

## Outdoor Parking

Stonco KEENE



### LytePro Garage & Canopy

- SpiroGuide light engine that reduces glare and increases uniformity
- Luminous white uplight option with a halo bezel that glows
- Dimming controls and UL924 emergency options
- Lightweight and "click!" no-screw surface mounting

Design  
ready

Stonco KEENE



### LytePro Area

- Mounting to round or square pole without need for accessories
- Large bolt spacing range for easy retrofit application
- Button or twist-lock photocell, motion response, and field adjustable wattage

Stock  
ready

Design  
ready

Stock  
ready

2 day  
shipping

Design  
ready

5-10 day  
shipping

# Retrofit options

## TLEDs

PHILIPS



### CorePro InstantFit Linear T5 & T8 LED Lamps

Simply replace traditional fluorescent lamps with budget friendly InstantFit TLED lamps to help save on energy costs.

Stock  
ready

PHILIPS



### MasterClass InstantFit Linear T5 & T8 LED Lamps

Install lamps with proven energy savings with the shatter-proof option that only Philips can offer.

Stock  
ready

PHILIPS



### CorePro MainsFit Linear T5 & T8 LED lamps

Bypass the ballast in fluorescent fixtures to upgrade your general lighting and conserve energy.

Stock  
ready

## TLEDs

PHILIPS



### MasterClass MainsFit Linear T5 & T8 LED lamps

Provide consistent light output for quality illumination and available in plastic for shatter prevention.

Stock  
ready

## Glass Lamps

PHILIPS



### Glass LED HID Replacement Lamps

Easy upgrade from HID lamps to LED with a seamless solution.

Stock  
ready

## High Bay Lamps

PHILIPS




### MasterClass TrueForce LED High Bay Lamps

Couple light distribution and high color rendering with energy efficiency to create a comfortable, safe and high productivity environment.

Stock  
ready





## LED Corn Cobs

**PHILIPS**



### CorePro LED Corn Cob

Maximize energy savings at an affordable price.

Stock  
ready

**PHILIPS**



### MasterClass TrueForce LED Corn Cob

Provide the "perfect fit" with uncompromising efficacy and color quality to keep outdoor areas brightly lit.

Stock  
ready

**PHILIPS**



### MasterClass LED Color-selectable Corn Cob lamps

Provide the "perfect fit" with uncompromising efficacy and color quality to keep outdoor areas brightly lit.

Stock  
ready

## LED Retrofit Kits

**PHILIPS**



### EvoKit Click

Easily upgrade existing fluorescent troffers to fast-track payback with energy-efficient LEDs in just 5 minutes.

Stock  
ready

# Get started with the Design Ready catalog



## Ready to create your vision?

Check out the Design Ready website and catalog for ordering information on the product families fit for bringing your Design Build project to life. Scan the QR code to learn more.







**GENLYTE  
SOLUTIONS**  
a Signify business



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone 800-555-0500

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.